



ABOUT US

 Novachem is a company established in Milan in 1998, as raw material suppliers.

In recent years Novachem has focused its activities on the formulation of products to provide its customers with innovative, customized solutions.







PRODUCTS

Highly concentrated solution of special dyes in water with outstanding performances in wood, leather and glass colouring



STRENGTHS



- High transparency
- High light fastness
- High colour strength
- No bleeding
- Metal free
- Not dangerous



DILUTION

Thanks to their high concentration the colorant of the series HYBRID can be diluted from 1:5 to 1:20 with the following solvents

- WATER
- ACETONE AND METHOXYPROPANOL
- METHOXYPROPANOL

- WATER AND ACETONE
- WATER AND METHOXYPROPANOL
- WATER AND ETANOL

The stability of above mentioned solutions is guaranteed up to ratio of 1:10 at any temperature condition from 5°C to + 50°C



OVERCOATIBILITY

All colours of the HYBRID series can be overcoated

SOLVENT BASED

- a) 2K PU system
- b) 2K Acrylic system
- c) UV Curing system

For resistance to Peroxides in the Redox Polyester we suggest a precautional test and if is necessary an application of a PU barrier is advisable

WATER BASED

- a) 1K system Acrylic and PU
- b) 2K system Acrylic and PU
- c) UV Curing system

With all-finishing systems the HYBRID colour series doesn't show any change in colour shade and colour strength and doesn't affect the curing time



LIGHT FASTNESS

XENOTEST 150 S (HERAUS)

Original Colour HRS 100

HRS 200



NOVAHYBRID BROWN SX 50

Application by sponge 1 layer without any protective varnishing

Test run by Xenotest 150 S device equipped with 1,3 kw xenon Air temperature= $50 \pm 5^{\circ}$ C Black panel temperature= $50 \pm 5^{\circ}$ C

XENOTEST 150 S (HERAUS)

Original Colour HRS 100

HRS 200



METAL COMPLEX DYES USED ON THE MARKET

Application by sponge 1 layer without any protective varnishing

Test run by Xenotest 150 S device equipped with 1,3 kw xenon Air temperature= $50 \pm 5^{\circ}$ C Black panel temperature= $50 \pm 5^{\circ}$ C-

